




Technical Information

PONTO 3 POWER






Scale 1:1

ON HEAD



ON SKULL SIMULATOR



*Curve compensation made for resonance on head.

Technical information Ponto 3 Power			
Battery voltage	1.1-1.5 V	Total harmonic distortion (THD60)	<3% above 600 Hz
Current consumption, In silence	1.35 mA	Equivalent Input noise	26 dB SPL
Current consumption, typical	2.20 mA	Electrical Input equivalent to an acoustic Input of 70 dB SPL	N/A*
Average battery lifetime	Typically 70-150 hours	Processing delay	6 ms
Frequency range (DIN45.605)	260 Hz-9.6 kHz	Battery size	675
Peak OFL at 90 dB SPL Input (skull sim.)	128 dB rel. 1 µN	Weight	17 g without battery
Peak OFL at 60 dB SPL Input (skull sim.)	116 dB rel. 1 µN	Physical dimensions (L*W*H)	34* 21* 14 mm
Peak OFL at 50 dB SPL Input (skull sim.)	106 dB rel. 1 µN	IRIL GSM/DECT	30/53 dB SPL

*Electrical audio input is available via wireless audio streaming from the Oticon Medical Streamer.