

Sina HYPE 6 G3

WITH BATTERY SIZE 10



 **Audio Service**

PRODUCT FEATURES

Semi-modular CIC

BASIC FEATURES

Battery compartment as on/off switch

Push button (integrated in battery compartment lid), can be programmed as a program button, program button with on/off function, volume control (only for binaural systems)

Level-dependent signal tones/melodies (activate/deactivate) for low battery voltage, program change, volume control, on/off function

Audiomatic power-on delay (P) (activate/deactivate)

Wax guard HF 3 Black or HF 4 Black

Microphone filter Microsafe

Removal line

OPTIONS



Audiostreamer Smart Connect

Remote control Smart Remote

Smart Connect App

Smart Remote App

PROGRAMMING CABLES

Programming cable, right

Art.-No. 105 40 984

Programming cable, left

Art.-No. 105 40 985

TECHNICAL FEATURES

16 signal processing channels / 8 frequency channels

8 AGC channels / 8 MPO channels

4 hearing programs

Data Logging

Wireless optional

➤ Binaural synchronization

➤ Wireless audio streaming

SIGNAL PROCESSING

Anti-Feedback system G3

Noise Manager

➤ Adaptive noise reduction

➤ Wiener filter

➤ Impulse suppressor

Frequency and dynamics concept


➤ TRC S

➤ Selective frequency compression

AUTOMATIC FUNCTIONS

Acclimatic

FITTING RANGE



P = Patent

For more information about features please check out our website www.audioservice.com

Sina HYPE 6 G3

Gain 55 dB



Audio Service



MAXIMUM OUTPUT

Input: 90 dB



MAXIMUM GAIN

Input: 50 dB

IEC 60118-7:2005¹⁾
ANSI S3.22-2009¹⁾



IEC 60118-0²⁾



TECHNICAL INFORMATION

MAXIMUM OUTPUT

Peak value at 90 dB	118 dB	127 dB
1,600 Hz (RTF)	110 dB	118 dB
HFA (High Frequency Average)	112 dB	115 dB

FULL ON GAIN

Peak value at 50 dB	55 dB	66 dB
1,600 Hz (RTF)	48 dB	56 dB
HFA (High Frequency Average)	48 dB	52 dB
Reference test gain	35 dB	49 dB

TECHNICAL FEATURES

Battery type	10	10
Battery life in hours	79	79
Frequency range	100 – 8,500 Hz	100 – 8,250 Hz
Battery current consumption	0.80 mA	0.80 mA
Equivalent noise level	19 dB	22 dB
Distortion		
500 Hz	1%	2%
800 Hz	1%	2%
1,600 Hz	1%	1%

¹⁾ Technical data measured in accordance with IEC 60118-7:2005 and ANSI S3.22-2009 at 2 ccm coupler

²⁾ Technical data measured in accordance with IEC 60118-0 at ear simulator



WARNING

Small parts present a choking hazard.
This device is not suitable for fitting to babies, small children or mentally disabled persons.

For control ranges and more programming features see Hearing Instrument Simulation of Connexx 8.1 and AudioFit 8.1 or higher.

Sina HYPE 6 G3

WITH BATTERY SIZE 10



 **Audio Service**

PRODUCT FEATURES

Semi-modular CIC

BASIC FEATURES

Battery compartment as on/off switch

Push button (integrated in battery compartment lid), can be programmed as a program button, program button with on/off function

Level-dependent signal tones/melodies (activate/deactivate) for low battery voltage, program change, on/off switch function

Audiomatic power-on delay (P) (activate/deactivate)

Wax guard HF 3 Black or HF 4 Black

Removal line

Microphone filter Microsafe

OPTIONS



Smart Remote App

PROGRAMMING CABLES

Programming cable, right

Art.-No. 105 40 984

Programming cable, left

Art.-No. 105 40 985

TECHNICAL FEATURES

16 signal processing channels / 8 frequency channels

8 AGC channels / 8 MPO channels

4 hearing programs

Data Logging

SIGNAL PROCESSING

Anti-Feedback system G3

Noise Manager

➤ Adaptive noise reduction

➤ Wiener filter

➤ Impulse suppressor

Frequency and dynamics concept


➤ TRC S

➤ Selective frequency compression

AUTOMATIC FUNCTIONS

Acclimatic

FITTING RANGE



P = Patent

For more information about features please check out our website www.audioservice.com

Sina HYPE 6 G3

Gain 71 dB



Audio Service


MAXIMUM OUTPUT

Input: 90 dB


MAXIMUM GAIN

Input: 50 dB

IEC 60118-7:2005¹⁾
ANSI S3.22-2009¹⁾



IEC 60118-0²⁾



TECHNICAL INFORMATION

MAXIMUM OUTPUT

Peak value at 90 dB	131 dB	138 dB
1,600 Hz (RTF)	129 dB	135 dB
HFA (High Frequency Average)	124 dB	128 dB

FULL ON GAIN

Peak value at 50 dB	71 dB	79 dB
1,600 Hz (RTF)	69 dB	77 dB
HFA (High Frequency Average)	65 dB	71 dB
Reference test gain	47 dB	70 dB

TECHNICAL FEATURES

Battery type	10	10
Battery life in hours	63	63
Frequency range	100 – 6,000 Hz	125 – 5,500 Hz
Battery current consumption	1.00 mA	1.00 mA
Equivalent noise level	17 dB	20 dB
Distortion		
500 Hz	1%	2%
800 Hz	1%	1%
1,600 Hz	1%	1%

¹⁾ Technical data measured in accordance with IEC 60118-7:2005 and ANSI S3.22-2009 at 2 ccm coupler

²⁾ Technical data measured in accordance with IEC 60118-0 at ear simulator



WARNING

Small parts present a choking hazard.
This device is not suitable for fitting to babies, small children or mentally disabled persons.



WARNING

The maximum output levels of the hearing systems can reach or exceed 132 dB SPL.
Risk of injury to the hearing of the wearer. Ensure that the hearing systems are fitted with care.

For control ranges and more programming features see Hearing Instrument Simulation of Connexx 8.1 and AudioFit 8.1 or higher.